



**Part Number: 9445**

Electronic, 5 C #20 Str TC, PVC Ins, PVC Jkt, CMG

[Request Sample](#)

**Product Description**

Electronic, 5 Conductor 20AWG (7x28) Tinned Copper, PVC Insulation, PVC Outer Jacket, CMG

**Technical Specifications**

**Physical Characteristics (Overall)**

**Conductor**

AWG	Stranding	Material	No. of Conductors
20	7x28	TC - Tinned Copper	5

Conductor Count: 5

**Insulation**

Material	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.015 in

**Color Chart**

Number	Color
1	Black
2	White
3	Red
4	Green
5	Brown

**Outer Shield Material**

Material
Unshielded

**Outer Jacket Material**

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.239 in	0.032 in

**Electrical Characteristics**

**Conductor DCR**

Nominal Conductor DCR
10.7 Ohm/1000ft

**Capacitance**

Nom. Capacitance Conductor to Conductor
27 pF/ft

**Current**

Max. Recommended Current [A]
3.2 Amps per conductor @ 25°C A

**Voltage**

<b>UL Voltage Rating</b>
300 V RMS

## Temperature Range

UL Temp Rating:	80°C (UL AWM Style 2464)
Operating Temp Range:	-20°C To +80°C

## Mechanical Characteristics

Bulk Cable Weight:	36 lbs/1000ft
Max Recommended Pulling Tension:	62 lbs
Min Bend Radius/Minor Axis:	2.5 in

## Standards

NEC/(UL) Specification:	CMG
CEC/C(UL) Specification:	CMG
UL AWM Style:	UL Style 2464 (300 V 80°C)
CPR Euroclass:	Eca

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

## Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1685 FT4 Loading
CSA Flammability:	FT4
ISO/IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Part Number

### Variants

Item #	Color	UPC	Footnote
9445 060100	Chrome	612825252481	
9445 0601000	Chrome	612825252498	C
9445 060500	Chrome	612825252504	C
9445 0605000	Chrome	612825252511	
9445 060U1000	Chrome	612825252467	

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

## History

Update and Revision:	Revision Number: 0.282 Revision Date: 08-22-2019
----------------------	--------------------------------------------------

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

