


[Back](#)

| Selected Cable: 17519             |                                                                                                                              |      |           |          | Cord View            |
|-----------------------------------|------------------------------------------------------------------------------------------------------------------------------|------|-----------|----------|----------------------|
| End View                          | Plug                                                                                                                         | Cord | Connector | End View |                      |
| NONE                              | 3"STRIP                                                                                                                      | SJT  | 2"STRIP   | C13      |                      |
| <b>Part Number</b>                | <b>17519</b>                                                                                                                 |      |           |          | <b>Approvals</b><br> |
| <b>NSN</b>                        | 5935-01-150-3107                                                                                                             |      |           |          |                      |
| <b>Category</b>                   | 3 conductor plastic original equipment cords                                                                                 |      |           |          |                      |
| <b>Shielding</b>                  | unshielded                                                                                                                   |      |           |          |                      |
| <b>Jacket Color</b>               | black                                                                                                                        |      |           |          |                      |
| <b>Length Feet</b>                | 9'10"                                                                                                                        |      |           |          |                      |
| <b>Length Meters</b>              | 3                                                                                                                            |      |           |          |                      |
| <b>Temperature Rating</b>         | 60 C°C                                                                                                                       |      |           |          |                      |
| <b>Packaging Units Per Carton</b> | H-100,H25                                                                                                                    |      |           |          |                      |
| <b>Color Coding</b>               | International                                                                                                                |      |           |          |                      |
| <b>AWG Stranding</b>              | 18 (41x34)                                                                                                                   |      |           |          |                      |
| <b>Nominal OD Inch</b>            | 0.315                                                                                                                        |      |           |          |                      |
| <b>Nominal OD millimeter</b>      | 8.00                                                                                                                         |      |           |          |                      |
| <b>Rating</b>                     | 1250 Watts 10A-125V (*)                                                                                                      |      |           |          |                      |
| <b>Notes</b>                      | See 17518 for 6'7" version. See 17521 for 16 gauge version. See 17619 for shielded version. 17519 is dual rated at 10A-250V. |      |           |          |                      |

Qty: 1

[Add to Quote](#)
[Back](#)

Volex Power Cord Products Division, 5350 Lakeview Parkway S. Drive #D Indianapolis, IN 46268  
800-246-CORD. [info@volexpowercords.com](mailto:info@volexpowercords.com)

Proposition 65 warning for California residents: This product contains chemicals, including lead, known to the State of California to cause (cancer, and) birth defects or other reproductive harm. Wash hands after handling.