




Back

**Selected Cable: 9483**

**Cord View**

End View	Plug	Cord	Connector	End View
				
NONE	NONE	SJO	NONE	NONE



<b>Part Number</b>	9483
<b>Category</b>	retractile cords
<b>Jacket Color</b>	Black
<b>Length Feet</b>	48
<b>Length Meters</b>	1.219 - 7.6
<b>Temperature Rating</b>	90 C°
<b>Packaging Units Per Carton</b>	S-5
<b>AWG Stranding</b>	18 (42x34)
<b>Nominal OD Inch</b>	0.385
<b>Nominal OD millimeter</b>	9.87
<b>Rating</b>	300V
<b>Notes</b>	4 Conductors. See 9482 for 12ft extended length version.

**Approvals**



Qty:

Back

Volex Power Cord Products Division, 5350 Lakeview Parkway S. Drive #D Indianapolis, IN 46268  
800-246-CORD. [info@volexpowercords.com](mailto:info@volexpowercords.com)

Proposition 65 warning for California residents: This product contains chemicals, including lead, known to the State of California to cause (cancer, and) birth defects or other reproductive harm. Wash hands after handling.

