

P624 Product Details

 Share  Print  Email

NEMA Terminal Blocks

[Not reviewed for RoHS Compliance](#)

Product Highlights:

- 600 Series Block Series
- NEMA Product Line
- Block Type = Flat Base
- Contact Configuration = Tubular Screw
- Medium Duty Application

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

No Image Available

P624

TE Internal Number: 6-1437393-9



[Superseded](#)



[Add to My Part List](#)



[Request Sample](#)



[Find Similar Products](#)



[Buy Product](#)

[Search for Replacement Parts](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Line Drawing](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Line = NEMA
- Screw Size = 10-32 Slotted Pan Head

Electrical Characteristics:

- Voltage Rating (VAC) = 300
- Amperes (A) = 50.0

Body Features:

- [Block Series](#) = 600 Series
- [Block Type](#) = Flat Base
- Mount Style = Direct Mount (Flat Base)
- [Wire Range \(Solid and Stranded\)\[MCM\] \(AWG\)](#) = 18-8
- [Blown Fuse Indicator](#) = Without
- [Blown Fuse Indicator Type](#) = None
- Wire Strip Length (mm [in]) = 8.74 [0.344]

Contact Features:

- Contact Configuration = Tubular Screw
- Pitch (mm [in]) = 9.53 [0.375]

Housing Features:

- [Housing Material](#) = Polypropylene

Industry Standards:

- [RoHS/ELV Compliance](#) = Not reviewed for ELV/RoHS compliance
- [Lead Free Solder Processes](#) = Not reviewed for lead free solder process

Operation/Application:

- Application = Medium Duty

Packaging Features:

- Terminals Per Foot = 30

Other:

- Brand = Buchanan

Corporate Information

[Who We Are](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

Quick Links

[Check Distributor Inventory](#)

[Cross Reference](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage your Account](#)

Keep Me Informed

Receive TE News, Events
& Technology Updates

Enter your email address

