

8134-HC-12P3-LF Product Details

[Share](#) |
 [Print](#) |
 [Email](#)



Discrete Sockets

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Mating Pin Dia. Range = .89 - 1.14 mm
- Socket Length = 4.06 mm
- Tin Contact Spring Plating
- Production Application
- Without Sealant

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

8134-HC-12P3-LF

(8-1437514-9)

TE Internal Number: 8-1437514-9

[Preliminary](#)

[View 3D PDF](#)

[Add to My Part List](#) |
 [Request Sample](#) |
 [Find Similar Products](#) |
 [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [HOLTITE CONTACTS](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [AUGAT HOLTITE Sockets](#) (PDF, English)

Application Specifications:

- [AUGAT HOLTITE Sockets](#) (PDF, English)

Instruction Sheets:

- None Available

CAD Files: [\(CAD Format & Compression Information\)](#)

- [2D Drawing](#) (DXF, Version C)
- [3D Model](#) (IGES, Version C)
- [3D Model](#) (STEP, Version C)

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Product Photo](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Socket Length \(mm \[in\]\)](#) = 4.06 [0.160]
- [Sealant](#) = Without
- Proprietary Name = HOLTITE
- Recommended Hole Size (mm [in]) = 2.08 [0.082]

Body Features:

- [Mating Pin Dia. Range \(mm \[in\]\)](#) = 0.89 - 1.14 [0.035 - 0.045]
- Spring Material = Beryllium Copper

Contact Features:

- [Contact Spring Plating](#) = Tin
- [Contact Base Material](#) = Beryllium Copper

Configuration Features:

- [Insertion Method](#) = Hand/Semi-Automatic

Industry Standards:

- Government/Industry Qualification = No
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Operation/Application:

- Application = Production

Packaging Features:

- [Packaging Method](#) = Loose Piece

Other:

- Brand = AMP

Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

