



+ CONNECTORS

STANDARD CIRCULAR CONNECTORS



✓ Active

TE CONNECTIVITY (TE)

T01-0580-S05-FEMALE REC PANEL MNT SOLDER

Triad 01 Connector System | Triad 01 , Triad 01 Panel/PCB Connector

1437720-3

TE Internal Number: 1437720-3

Alias ID: T01-0580-S05

EU RoHS Compliant

EU ELV Compliant

Product Type Connector

Number of Positions 5

Sealable Yes

Wire/Cable Size .25 mm² [24 AWG]

Connector Style Receptacle

 **PRODUCT DRAWING**
English

DOCUMENTATION

Product Drawings

T01 FEMALE CONN.PANEL MNT.SOLDER VER.5 POS. T01 BUCHSENSTECKER,EINBAU, LOETVER.5 POL.

PDF (TIFF AVAILABLE)

English

T01 FEMALE PLUG CONN.PANEL MNT.SOLDER VER. 3-8 POS. 180 DGR. T01 BUCHSENSTECKER,EINBAU,LOETVERSION 3-8 POL.180 GRAD

PDF (TIFF AVAILABLE)

English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Product Type Connector

Sealable Yes

Connector Style Receptacle

Configuration Features

Number of Positions 5

Electrical Characteristics

Operating Voltage (VAC) 60

Contact Features

Contact Type Socket

Dimensions

Wire/Cable Size .25 mm² [24 AWG]

Assembly Length (mm) 17.7

Usage Conditions

Operating Temperature Range (°C) -40 – 80

Industry Standards

UL Flammability Rating UL 94V-2

Packaging Features

Packaging Quantity 25

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
