


322-HCS5P2-100 Product Details

[Live Product Chat](#)



Discrete Sockets

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- Socket
- Mating Pin Dia. Range = .28 - .46 mm
- Socket Length = 2.54 mm
- Gold Contact Spring Plating
- Production Application

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

322-HCS5P2-100

TE Part Number: 2-1437514-0

[Active](#)

[Add to Part List](#)

Documentation & Additional Information

Product Drawings:

- [ASSEMBLY, HOLTITE, REELED](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [AUGAT* HOLTITE* Sockets](#) (PDF, English)

Application Specifications:

- [AUGAT HOLTITE Sockets](#) (PDF, English)

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Product Photo](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Socket
- [Socket Length \(mm \[in\]\)](#) = 2.54 [0.100]
- [Sealant](#) = Without
- Proprietary Name = HOLTITE
- Recommended Hole Size (mm [in]) = 1.15 [0.0453]

Body Related Features:

- [Mating Pin Dia. Range \(mm \[in\]\)](#) = 0.28 - 0.46 [0.011 - 0.018]
- Spring Material = Beryllium Copper

Contact Related Features:

- [Contact Spring Plating](#) = Gold
- [Contact Material](#) = Beryllium Copper

Configuration Related Features:

- [Insertion Method](#) = Hand/Semi-Automatic/Automatic

Industry Standards:

- Government/Industry Qualification = No
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Operation/Application:

- Application = Production

Packaging Related Features:

- Packaging Method = Reel
- Packaging Quantity = 2,500/Reel

Other:

- Brand = AMP

[Provide Website Feedback](#) | [Need Help?](#)