


3WWV-02-004 Product Details

[Live Product Chat](#)



3WWV-02-004

TE Part Number: 3-1437647-4

Superseded

[Add to Part List](#)
[Search for Replacement Parts](#)

Barrier Strips, Barrier Strip Sockets

[Not reviewed for RoHS Compliance](#)

Product Highlights:

- Barrier Strip
- Barrier Style = Single Row, Tri-Barrier
- Block Style = Open Bottom with Standoffs
- 6.35 mm Centerline
- Vertical Mount Angle

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Barrier Strip
- [Mount Angle](#) = Vertical
- Number of Positions = 2
- CSA File No. = LR30811
- UL Recognized = File No. E54800
- Screw Material = Steel
- Mounting Ears = Without
- Comment = Other options available upon request, consult our Product Information Center.

Mechanical Attachment:

- Screw Plating = Bright Zinc/Chrome
- Mounting Style = Open End Position

Electrical Characteristics:

- [Top Hardware](#) = Wire Clamp Combo Head
- Number of Levels = Single
- End Barriers = With
- Bracket = Without
- Screw Head Type = Slotted
- Voltage (VAC) = 300
- Current Rating, Max. (Amps.) = 10
- Mounting Insert = Without

Termination Related Features:

- Terminal Plating = Bright Tin

Body Related Features:

- [Barrier Style](#) = Single Row, Tri-Barrier
- Block Style = Open Bottom with Standoffs
- [Centerline \(in \[mm\]\)](#) = 0.250 [6.35]
- Number of Rows = Single
- [Terminal Style](#) = Solderless Wire Wrap
- Terminal Material = Copper Alloy
- Flammability Rating = UL 94V-0
- Wire Range (mm [AWG]) = 0.05-1.40² [30-16]

Contact Related Features:

- Mounting Options = None

Housing Related Features:

- Housing Material = Polypropylene
- Housing Color = Black

Industry Standards:

- [RoHS/ELV Compliance](#) = Not reviewed for ELV/RoHS compliance
- [Lead Free Solder Processes](#) = Not reviewed for lead free solder process

Other:

- Brand = Buchanan