

 Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- ? 444 Series Block Series
 ? Terminal Block
 ? Ultra Heavy Duty Application
 ? Contact Type = Tubular Screw
 ? Mount Style = Direct Mount (Flat Base)

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

444

TE Part Number: 1 - 1437396 - 0

 Obsolete

-  [Add to Part List](#)
[Contact Product](#)
[Information Center](#)

Documentation & Additional Information

Documents are temporarily unavailable. We are working hard to correct the problem. Please try again later.

Additional Information:

- ## ? Product Line Information

Additional Product Images:

- ## ? Typical Assembly View

Related Products:

- ## ? Tooling

Product Features

Product Type Features:

- ? Product Type = Terminal Block
? Screw Size = 15/16 -16 Hex Socket Set Screw

Electrical Characteristics:

- ? Voltage Rating (VAC) = 600
- ? Amperes (Amps.) = 455.0

Body Related Features:

- ? Block Series = 444 Series
- ? Mount Style = Direct Mount (Flat Base)
- ? Wire Range (Solid and Stranded)[MCM] (AWG)
= 4 - 600 kcmil (MCM)
- ? Blown Fuse Indicator = Without
- ? Blown Fuse Indicator Type = None
- ? Wire Strip Length (mm [in]) = 34.93 [1.375]
- ? Flammability Rating = UL 94V -1

Contact Related Features:

- ? Contact Type = Tubular Screw
? Pitch (mm [in]) = 60.45 [2.380]

Housing Related Features:

- ? Housing Material = Phenolic

Industry Standards:

- ? RoHS/ELV Compliance = RoHS compliant, ELV compliant
- ? Lead Free Solder Processes = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? Temperature, Max. (°C) = 150

Operation/Application:

- ? Application = Ultra Heavy Duty

Packaging Related Features:

- ? Terminals Per Foot = 5

Other:

- ? Brand = Buchanan