


6PCV - 11 Product Details

 [Live Product Chat](#)

6PCV - 11

TE Part Number: 4 - 1437653 - 2

 [Superseded](#)
[Add to Part List](#)
[Search for Replacement Parts](#)

Barrier Strips, Barrier Strip Sockets

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Barrier Strip
- ? Barrier Style = Single Row, Tri -Barrier
- ? Block Style = Open Bottom with Standoffs
- ? 9.53 mm Centerline
- ? Vertical Mount Angle

[View all Features](#) | [Find Similar Products](#)

Quick Links

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? None Available

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Barrier Strip
- ? [Mount Angle](#) = Vertical
- ? Number of Positions = 11
- ? CSA File No. = LR30811
- ? UL Recognized = File No. E54800
- ? Screw Material = Steel
- ? Mounting Ears = Without
- ? Comment = Do not order Screw and Captive Clamp in combination with other top hardware.; Other options available upon request, consult our Product Information Center.

Mechanical Attachment:

- ? Screw Plating = Bright Zinc/Chrome
- ? Mounting Style = Direct (All Positions Filled)

Electrical Characteristics:

- ? [Top Hardware](#) = Wire Clamp Combo Head
- ? Number of Levels = Single
- ? End Barriers = Without
- ? Bracket = Without
- ? Screw Head Type = Slotted
- ? Mounting Insert = Without

Body Related Features:

- ? [Barrier Style](#) = Single Row, Tri -Barrier
- ? Block Style = Open Bottom with Standoffs
- ? [Centerline \(in \[mm\]\)](#) = 0.375 [9.53]
- ? Number of Rows = Single
- ? [Terminal Style](#) = Printed Circuit Pin 5.08 [.200]

Contact Related Features:

- ? Mounting Options = None

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not reviewed for lead free solder process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- ? Brand = Buchanan