



+ CONNECTORS

STANDARD CIRCULAR CONNECTORS



✓ Active

TE CONNECTIVITY (TE)

T01-0580-P08-MALE REC PANEL MOUNT SOLDER

Triad 01 Connector System | Triad 01 , Triad 01 Panel/PCB Connector

9-1437719-3

TE Internal Number: 9-1437719-3

Alias ID: T01-0580-P08

EU RoHS Compliant

EU ELV Compliant

Product Type Connector

Shell Material CuZn

Wire/Cable Size (mm²) .14

Sealed Yes

Connector Style Plug

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**

DOCUMENTATION

Product Drawings

T01 MALE CONN.PANEL MNT.SOLDER VER.8 POS. T01 STIFTSTECKER,EINBAU,LOETVERS.8 POL.

PDF (TIFF AVAILABLE)

English

T01 MALE PLUG CONN. PANEL MNT. SOLDER VER. 3-8 POS. 180 DGR. T01 STIFTSTECKER,EINBAU,LOETVERS. 3-8 POL. 180 GRAD

PDF (TIFF AVAILABLE)

English

CAD Files

Customer View Model

2D_DXF.ZIP

English

3D PDF

PDF

3D

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Product Type Connector

Sealed Yes

Connector Style Plug

Configuration Features

Number of Positions 8

Electrical Characteristics

Operating Voltage (VAC) 60

Body Features

Shell Material CuZn

Contact Features

Contact Type Pin

Dimensions

Wire/Cable Size (mm²) .14

Assembly Length (mm) 24.4

Usage Conditions

Operating Temperature Range (°C) -40 – 80

Industry Standards

UL Flammability Rating UL 94V-2

Packaging Features

Packaging Quantity 25

Statement of Compliance

Statement of Compliance

PDF