



CONNECTORS

STANDARD CIRCULAR CONNECTORS



✓ Active

TE CONNECTIVITY (TE)

T01-0580-S03-FEMALE REC PANEL MNT SOLDER

Triad 01 Connector System | Triad 01 , Triad 01 Panel/PCB Connector

9-1437719-6

TE Internal Number: 9-1437719-6

Alias ID: T01-0580-S03

EU RoHS Compliant

EU ELV Compliant

Product Type Connector

Sealable Yes

Shell Material CuZn

Number of Positions 3

Operating Temperature Range (°C) -40 – 80

[↓ PRODUCT DRAWING](#)
English

[↓ 3D PDF](#)

DOCUMENTATION

Product Drawings

**T01 FEMALE PLUG CONN.PANEL MNT.SOLDER VER. 3-8 POS. 180 DGR. T01
BUCHSENSTECKER,EINBAU,LOETVERSION 3-8 POL.180 GRAD**

PDF (TIFF AVAILABLE)

English

CAD Files

3D PDF

PDF

English

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Product Type Connector

Sealable Yes

Connector Style Receptacle

Configuration Features

Number of Positions 3

Electrical Characteristics

Operating Voltage (VAC) 60

Body Features

Shell Material CuZn

Contact Features

Contact Type Socket

Dimensions

Wire/Cable Size .25 mm² [24 AWG]

Assembly Length (mm) 17.7

Usage Conditions

Operating Temperature Range (°C) -40 – 80

Industry Standards

UL Flammability Rating UL 94V-2

Packaging Features

Packaging Quantity 25

Statement of Compliance

Statement of Compliance

PDF