

## TSB100003DS Product Details



**TSB100003DS**  
(3-1437387-9)

TE Internal Number: 3-1437387-9

 **Superseded**

[Search for Replacement Parts](#)

### Europa Terminal Blocks

 [Converted to EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- 12.00 mm Centerline
- Number of Circuits = 3
- Wire Range = 0.30-6.00<sup>2</sup> [22-10] mm [AWG]
- With Wire Protection
- Integrated Fuse = No

[View all Features](#)

### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

 [Add to My Part List](#)
 [Request Sample](#)
 [Find Similar Products](#)
 [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Number of Circuits](#) = 3
- [Integrated Fuse](#) = No
- Color = Natural
- Screw Size = M3.5
- Screw Material = Steel
- CSA File Number = LR28387
- UL File Number = E60677

#### Mechanical Attachment:

- Screw Plating = Bright Zinc/Chrome

#### Electrical Characteristics:

- Current Rating (A) = 40
- Voltage Rating (VAC) = 250
- Wire Protector Material = Stainless Steel

#### Body Related Features:

- [Centerline \(mm \[in\]\)](#) = 12.00 [0.472]
- [Wire Range \(mm \[AWG\]\)](#) = 0.30-6.00<sup>2</sup> [22-10]
- [Wire Protection](#) = With
- [Ground](#) = Without
- [Series](#) = TSB1000

#### Contact Related Features:

- Contact Base Material = Brass
- Contact Plating, Mating Area, Material = Tin

#### Housing Related Features:

- Housing Material = Polyamide - GF
- UL Flammability Rating = UL 94V-2

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

#### Conditions for Usage:

- [Temperature Range \(°C\)](#) = 100

#### Other:

- Brand = Buchanan

 [BOOKMARK](#) 

### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat with Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage Your Account](#)

### Sign up for our eNewsletter

Enter your email address

### Follow Us On:



### Visit Us On:

