

PowerMark® Label Materials

www.BradyID.com/powermark

Benchtop Printers

Phosphorescent Tape (B-526)

- High-intensity; glows brighter and longer than B-582
- Permanent adhesive and glows in darkness for 10 hours
- Complies with indoor use requirements specified in RS 6-1 and 6-1A of New York Local Law 26



Figure 33



Diagram	Catalog #	B#	Color	Label Width A Inch (mm)	Roll Length B Inch (mm)	Labels Per Roll
Fig. 33	105912	B-526	Phosphorescent	4.000 (101.6)	33 ft. (10.1m)	1 Roll (cont.)
Fig. 33	105913	B-526	Phosphorescent	7.000 (178.0)	33 ft. (10.1m)	1 Roll (cont.)
Fig. 33	105914	B-526	Phosphorescent	10.000 (254.0)	33 ft. (10.1m)	1 Roll (cont.)

Glow-In-The-Dark Phosphorescent (B-582)

- Permanent adhesive and glows for hours in darkness
- Meets ISO, DIN and ASTM standards



Figure 33



Diagram	Catalog #	B#	Color	Label Width A Inch (mm)	Roll Length B Inch (mm)	Labels Per Roll
Fig. 33	13582	B-582	Phosphorescent	4.000 (101.6)	33 ft. (10.1m)	1 Roll (cont.)
Fig. 33	13587	B-582	Phosphorescent	7.000 (178.0)	33 ft. (10.1m)	1 Roll (cont.)
Fig. 33	13592	B-582	Phosphorescent	10.000 (254.0)	33 ft. (10.1m)	1 Roll (cont.)



Spare ribbon cassette (holder)
Catalog # 13507



PowerMark® Industrial Grade Print Ribbons

- Super-tough, smear-proof ribbons ensure your printed text lasts for years outdoors and in industrial areas
- 2 and 4-color “paneled” ribbons are used to print labels & signs with more than 1 print color

Single Color Print Ribbons

Catalog #	Color	Size Inch (mm)	Length
13511	Black	6.250 (158.0)	200 ft. (60.9 m)
13510	Black	8.800 (224.0)	200 ft. (60.9 m)
13513	White	6.250 (158.0)	200 ft. (60.9 m)
13512	White	8.800 (224.0)	200 ft. (60.9 m)
13595	Red	6.250 (158.0)	200 ft. (60.9 m)
13514	Red	8.800 (224.0)	200 ft. (60.9 m)
13596	Blue	6.250 (158.0)	200 ft. (60.9 m)
13515	Blue	8.800 (224.0)	200 ft. (60.9 m)
13597	Green	6.250 (158.0)	200 ft. (60.9 m)
13516	Green	8.800 (224.0)	200 ft. (60.9 m)
13598	Magenta	6.250 (158.0)	200 ft. (60.9 m)
13517	Magenta	8.800 (224.0)	200 ft. (60.9 m)
13599	Yellow	6.250 (158.0)	200 ft. (60.9 m)
13518	Yellow	8.800 (224.0)	200 ft. (60.9 m)
13600	Orange	6.250 (158.0)	200 ft. (60.9 m)
13519	Orange	8.800 (224.0)	200 ft. (60.9 m)

Two Color Paneled Print Ribbons

Catalog #	Color	Size Inch (mm)	Color Panel Size Inch (mm)	Length
8" Panels used to create 2 color signs up to 8" long				
13523	Black & Red	6.250 (158.0)	8.000 (203.2) Panels	200 ft. (60.9 m)
13522	Black & Red	8.800 (224.0)	8.000 (203.2) Panels	200 ft. (60.9 m)
13527	Black & Yellow	6.250 (158.0)	8.000 (203.2) Panels	200 ft. (60.9 m)
13529	Black & Orange	6.250 (158.0)	8.000 (203.2) Panels	200 ft. (60.9 m)
13704	Black & Green	6.250 (158.0)	8.000 (203.2) Panels	200 ft. (60.9 m)
13706	Black & Green	8.800 (224.0)	8.000 (203.2) Panels	200 ft. (60.9 m)
15" Panels used to create 2 color signs up to 15" long				
13521	Black & Red	6.250 (158.0)	15.000 (381.0) Panels	200 ft. (60.9 m)
13520	Black & Red	8.800 (224.0)	15.000 (381.0) Panels	200 ft. (60.9 m)
13525	Black & Blue	6.250 (158.0)	15.000 (381.0) Panels	200 ft. (60.9 m)
13524	Black & Blue	8.800 (224.0)	15.000 (381.0) Panels	200 ft. (60.9 m)
13526	Black & Yellow	8.800 (224.0)	15.000 (381.0) Panels	200 ft. (60.9 m)
13528	Black & Orange	8.800 (224.0)	15.000 (381.0) Panels	200 ft. (60.9 m)
13705	Black & Green	6.250 (158.0)	15.000 (381.0) Panels	200 ft. (60.9 m)
13707	Black & Green	8.800 (224.0)	15.000 (381.0) Panels	200 ft. (60.9 m)

Four Color Paneled Print Ribbons

Catalog #	Color	Size Inch (mm)	Color Panel Size Inch (mm)	Length
8" Panels used to create 4 color signs up to 8" long				
13533	Blk/Red/Blue/Yel	6.250 (158.0)	8.000 (203.2) Panels	200 ft. (60.9 m)
13532	Blk/Red/Blue/Yel	8.800 (224.0)	8.000 (203.2) Panels	200 ft. (60.9 m)
13537	Blk/Red/Blue/Grn	6.250 (158.0)	8.000 (203.2) Panels	200 ft. (60.9 m)
13536	Blk/Red/Blue/Grn	8.800 (224.0)	8.000 (203.2) Panels	200 ft. (60.9 m)
51448	Blk/Red/Org/Blue	8.800 (224.0)	8.000 (203.2) Panels	200 ft. (60.9 m)
15" Panels used to create 4 color signs up to 15" long				
13531	Black/Red/Blue/Yellow	6.250 (158.0)	15.000 (381.0) Panels	200 ft. (60.9 m)
13530	Black/Red/Blue/Yellow	8.800 (224.0)	15.000 (381.0) Panels	200 ft. (60.9 m)
13535	Black/Red/Blue/Green	6.250 (158.0)	15.000 (381.0) Panels	200 ft. (60.9 m)
13534	Black/Red/Blue/Green	8.800 (224.0)	15.000 (381.0) Panels	200 ft. (60.9 m)