

BRADY B-569 HIGH PERFORMANCE POLYESTER TAPE

TDS No. B-569

Effective Date: 08/26/2011

Description:

Brady B-569 is a polyester label stock with permanent pressure sensitive adhesive.

Details:



Use:

Brady B-569 is designed for use with the Brady Labelizer® Plus Industrial Labeling System and the VersaPrinter™ Label and Sign Maker System, PowerMark® Sign and Label Maker and GlobalMark™ Industrial Label Maker. Brady B-569 is designed for use on stainless steel pipes in harsh environments such as the Pulp and Paper Industry.

Adhesive Type:

Permanent pressure sensitive acrylic

Substrate Type:

Polyester film

Standard Material Colors:

White, clear, yellow, blue, red, green, and magenta

Standard Legend Colors:

Black, white, red, and magenta

Thickness (PSTC-33):

Total: 0.003 in. (0.076mm)

Tensile Strength (PSTC-31):

45 lb/in. (790 N/100mm)

Elongation (PSTC-31):

80%

Adhesive Properties:

Adhesion to Steel (PSTC-1)

15 Minute Dwell (Avg.) -- 60 oz/in. (65 N/100mm)

Ultimate Dwell (72 Hrs.) (Avg.) -- 75 oz/in. (82N/100mm)

Tack (ASTM D 2979) (Avg.) -- 1000 g

Abrasion Resistance (Method 5306 of U.S. Federal Test Method Std. No. 191A):

CS-10 wheels, 250 g wts.

The printed legend withstands up to 100 cycles.

CS-17 wheels, 1000 g wts.

Substrate withstands over 3000 cycles.

Gloss:

80 Gardner Units (100+ Gardner Units on clear)

Minimum Application Temperature:

0°F (-18°C)

Service Temperature:

-40°F to 212°F (-40°C to 100°C)

Average Outdoor Durability:

3 to 5 years

Chemical Resistance:

REAGENT	7 DAY IMMERSION	DIP TEST	RUB TEST
30% Sulfuric Acid	NE	NE	NE
10% Sulfuric Acid	NE	NE	NE
30% HCl	NE	NE	NE
10% HCl	NE	NE	NE
50% NaOH	F	NE	NE
10% NaOH	F	NE	NE
Methyl Ethyl Ketone	F	F	F
Acetone	F	F	F
1,1,1-Trichloroethane	F	F	F
Methanol	F	NE	F
IPA (Isopropanol)	F	NE	NE
ASTM #3 Oil	NE	NE	NE
SAE 20 Oil	NE	NE	NE
Alconox®	NE	NE	NE
Toluene	F	F	F
Mineral Spirits	NE	NE	NE
Glacial Acetic Acid	F	NE	F
5% Acetic Acid	NE	NE	NE
Diesel Fuel	NE	NE	F
Heptane	F	NE	F
Cellosolve Acetate	F	F	F
Conc. Ammonia	NE	NE	NE
10% Ammonia	NE	NE	NE
Turpentine	F	NE	F
Kerosene	NE	NE	NE
Water	NE	NE	NE
Gasoline	F	NE	F

NE = No Effect

NT = Not Tested

F = Failed (affected Sample)

7 Day Immersion: Immersed in reagent for 7 days.

Dip Test: Five 10 minute dips in reagent with 30 minute recovery.

Rub Test: Rubbed sample for 30 seconds with swab soaked in reagent.

Product testing, customer feedback, and history of similar products, support a customer performance expectation of at least **two years from the date of receipt** for this product as long as this product is stored in its original packaging in an environment *below 80 degrees F (27°C) and 60% RH*. We are confident that our product will perform well beyond this time frame. However, it remains the responsibility of the user to assess the risk of using such product. We encourage customers to develop functional testing protocols that will qualify a product's fitness for use, in their actual applications.

Trademarks:

ASTM: American Society for Testing and Materials (U.S.A.)

Alconox® is a registered trademark of Alconox Co.

All S.I. Units (metric) are mathematically derived from the U.S. Conventional

Globalmark® is a registered trademark of Brady Worldwide, Inc.

Labelizer® is a registered trademark of Brady Worldwide, Inc.

PSTC: Pressure Sensitive Tape Council (U.S.A.)

PowerMark® is a registered trademark of Brady Worldwide, Inc.

SAE: Society of Automotive Engineers (U.S.A.)

Signmark® is a registered trademark of Brady Worldwide, Inc.
Units.

VersaPrinter™ is a trademark of Brady Worldwide, Inc.

Note: All values shown are averages and should not be used for specification purposes.

Test data and test results contained in this document are for general information only and shall not be relied upon by Brady customers for designs and specifications, or be relied on as meeting specified performance criteria. Customers desiring to develop specifications or performance criteria for specific product applications should contact Brady for further information.

Product compliance information is based upon information provided by suppliers of the raw materials used by Brady to manufacture this product or based on results of testing using recognized analytical methods performed by a third party, independent laboratory. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

WARRANTY

Brady products are sold with the understanding that the buyers will test them in actual use and determine for themselves their adaptability to their intended uses. Brady warrants to the buyers that its products are free from defects in material and workmanship, but limits its obligation under this warranty to replacement of the product shown to Brady's satisfaction to have been defective at the time Brady sold it. This warranty does not extend to any persons obtaining the product from the buyers. This warranty is in lieu of any other warranty, express or implied, including, but not limited to, any implied warranty of merchantability or fitness for a particular purpose, and of any other obligations or liability on Brady's part. Under no circumstances will Brady be liable for any loss, damage, expense, or consequential damages of any kind arising in connection with the use, or inability to use, Brady's products.

Copyright 2016 Brady Worldwide, Inc. | All Rights Reserved
Material may not be reproduced or distributed in any form without written permission.

Brady North America | 6555 W. Good Hope Rd | Milwaukee, WI 53223 | USA | Tel: 414-358-6600 | Fax: 800-292-2289