


 All Categories

 0 item(s) | \$0.00

Products | Standards and Compliance | Customer Support | Technical Support

Home > Labels and Tapes > Printer Labels and Ribbons > Desktop Printer Labels > BBP33 Label Printer Labels >



Zoom



PermaSleeve® PS Polyolefin Wire Marking Sleeves - White

Part Number: B33D-187-2-342
Product Number: 143023
Material Description: PermaSleeve® Heat-Shrink Polyolefin
QTY/UOM: 750/Roll

Overview | Specifications

Specifications for PermaSleeve® PS Polyolefin Wire Marking Sleeves - White

Part Number	B33D-187-2-342
Agency Approval(s)/Compliance	SAE-AMS-DTL-23053/5 (class 1), SAE-AS-81531, MIL-STD-202, Tested per ASTM E162, ASTM E662
Application	Panel Identification, Wire & Cable Marking
Brady Material Number	B-342
Color	White
Description	PermaSleeve® PS Polyolefin Wire Marking Sleeves - White
Finish	Matte
Height (in)	0.335"
Height (mm)	8.510 mm
Label Type/Style	Sleeve
Material Description	PermaSleeve® Heat-Shrink Polyolefin
Material Type	Polyolefin
Printable Sides	Two-Side Printable
Printer Compatibility	BBP33
Product Number	143023
Qty Per Row	1
QTY/UOM	750/Roll
Range of Wire Diameter (in)	0.062" - 0.150"
Range of Wire Diameter (mm)	1.60 mm - 3.80 mm
Recommended Ribbon Series	R6600 Series
Safety Catalog	pg. 375
Shrink Ratio	3 to 1
Slit Sleeves	No
Special Properties	Heat-shrinkable, Self-extinguishing
Suggested Ribbon Part#	B30-R6600
UPC Code	66282096863
Vertical Repeat	0.625" (15.88 mm)
Web Width	3.490" (88.65 mm)
Width (in)	2.000"
Width (mm)	50.800 mm
Wire Gauge	20 to 10
RoHS Compatibility	Pass 2011/65/EU

CONTACT
 Contact Us
 Email Subscription
 International Sites

ABOUT
 Company Information
 News & Events

CORPORATE INFORMATION
 Privacy Policy
 Terms of Use

SOCIAL
 Facebook
 Twitter
 YouTube

