



WELCOME TO BRADY [My Account](#)
[Register/Login](#) **888-250-3082** [Contact Us](#)
[Find a Distributor](#)

[MY CART](#)

[Home](#) [Products](#) [Labels and Tapes](#) [Labels](#) [Product ID Labels](#) [Barcode and Tracking Labels](#) [Inventory and WIP Labels](#) [EMAIL PAGE](#) [PRINT PAGE](#)

TLS 2200®/TLS PC Link™ Labels

Questions?
1.888.250.3082



TLS 2200®/TLS PC Link™ Labels - # PTL-15-498

SIZE: 1.000" W x 0.275" H (25.400 mm W x 6.990 mm H)
MATERIAL: Repositionable Vinyl Cloth
QTY/UOM: 750/Roll
CATALOG #: PTL-15-498
PRODUCT #: 62661



[OVERVIEW](#) [SPECIFICATIONS](#)

Description for TLS 2200®/TLS PC Link™ Labels

Labels for the TLS 2200® & TLS-PC Link™ Thermal Transfer Portable Printers. Please Note: This material is UL recognized with its respective ribbon. See the "Recommended Ribbon Series" for the appropriate ribbon to use.

Specification Of TLS 2200®/TLS PC Link™ Labels

Application(s): Barcoding, Component ID, Equipment ID, General Identification, General Purpose ID, Through Hole - Top, Wire & Cable Marking

Agency Approval(s)/Compliance: UL Recognized

Size: 1.000" W x 0.275" H (25.400 mm W x 6.990 mm H)

Printable Area: 1.000" W x 0.275" H (25.400 mm W x 6.990 mm H)

Max Characters Per Line For Font #2: 24

Max Lines of Text For Font #2: 2

Label Type/Style: Label

Color: White

Finish: Semi-Gloss

Qty Per Row: 1

Material Type: Vinyl Cloth

Material Description: Repositionable Vinyl Cloth

Brady Material #: [B-498](#)

Safety Catalog: [pg. 280](#)

General ID Catalog: [pg. 45](#)

Recommended Ribbon Series: R6210

Suggested Ribbon Part#: R6210

Acceptable Ribbon Series: R4310

After Process: Yes, this material will work with this application

Printer Compatibility: BMP71, TLS 2200, TLS-PC Link

Surface: Smooth, Textured/Rough

Surface Mount Technology: No, this material does not work with this application

Through Hole Technology: Top: Yes. In extreme high temperatures, testing of this material is recommended, Bottom: No

Special Properties: Repositionable

RoHS Compatibility: Pass 2002/95/EC

QTY/UOM: 750/Roll

<p>Customer & Tech Support Find a Distributor Submit Product Feedback Submit Website Feedback Contact Us Site Map</p>	<p>Distribution Partners Bradyserve.com BradyDistributor.com Minimum Advertised Price Policy</p>	<p>Corporate Info About Brady Bradycorp.com Privacy Policy Legal Information ISO14001 Certified ISO9001 Certified Terms of Use Terms and Conditions of Sale</p>	<p>Brady International Sites</p> <table> <tr> <td>Canada</td> <td>Brazil</td> <td>Europe, Africa, Middle East</td> </tr> <tr> <td>Canada (Français)</td> <td>Asia</td> <td></td> </tr> <tr> <td>Latin America</td> <td>Australia</td> <td></td> </tr> </table>	Canada	Brazil	Europe, Africa, Middle East	Canada (Français)	Asia		Latin America	Australia	
Canada	Brazil	Europe, Africa, Middle East										
Canada (Français)	Asia											
Latin America	Australia											

Brady identifies and protects products, people, and premises with high performance labels, industrial label printers, software, safety & facility identification, spill control, Lockout Tagout solutions and more. Brady helps you create and maintain safer work environments and comply with regulatory standards. Our high-performance materials clearly identify products, components and other assets, even in the most extreme conditions.



©2014 Brady Worldwide, Inc.



Safe & Secure Online Shopping