

BRADY B-422 THERMAL TRANSFER PRINTABLE GLOSSY WHITE POLYESTER LABEL STOCK

TDS No. B-422

Effective Date: 01/18/2019

Description:

GENERAL

Print Technology: Thermal transfer

Materials Type: White polyester

Finish: Glossy white

Adhesive: Permanent acrylic

APPLICATIONS

Electronic PCB and component identification, bar code label and rating plates and solar panel identification.

RECOMMENDED RIBBONS

Brady Series R6000 Halogen Free

Brady Series R4400 (colors- red, blue, green, white)

Brady Series R4900 (alternate)

REGULATORY/AGENCY APPROVALS

UL: B-422 is a UL Recognized Component to UL969 Labeling and Marking Standard when printed with the Brady Series R6000 Halogen Free and Brady Series R4900 ribbons. See UL file MH17154 for specific details. UL information can be accessed on line at UL.com in the UL Product iQ area.

CSA: B-422 is CSA Accepted to C22.2 No.0.15-95 Adhesive Labels Standard when printed with the Brady Series R6000 ribbon. See CSA file 041833 for specific details. CSA information can be accessed online at directories.csa-international.org.

For information on the Weee-RoHS compliance status for a Brady Product go to one of the following websites:

In Canada: www.bradycanada.ca/weee-rohs

In Europe: www.bradyeurope.com/rohs

In Japan: www.bradyc.co.jp/products/labelsuse/rohs

All other regions: www.bradyd.com/weee-rohs

SPECIAL FEATURES

B-422 is designed to withstand exposure to numerous solvents and exhibits good adhesion to many surfaces including low surface energy plastics.

B-422 is UL Recognized for Outdoor Use on glass, thermoset polyester plastic and polyvinyl fluoride plastic surfaces to support solar panel identification applications.

Details:

PHYSICAL PROPERTIES	TEST METHODS	AVERAGE RESULTS
Thickness	ASTM D 1000 -Substrate -Adhesive -Total (excluding liner)	0.002 inch (0.0508 mm) 0.002 inch (0.0508 mm) 0.004 inch (0.1016 mm)
Adhesion to:	ASTM D 1000	
-Stainless Steel	20 minute dwell 24 hour dwell	47 oz/inch (51 N/100 mm) 55 oz/inch (60 N/100 mm)
-Textured ABS	20 minute dwell 24 hour dwell	30 oz/inch (33 N/100 mm) 35 oz/inch (38 N/100 mm)
-Polypropylene	20 minute dwell 24 hour dwell	47 oz/inch (51 N/100 mm) 51 oz/inch (55 N/100 mm)
-Enamel Painted Metal	20 minute dwell 24 hour dwell	54 oz/inch (59 N/100 mm) 61 oz/inch (67 N/100 mm)
-Powder Coated Metal	20 minute dwell 24 hour dwell	45 oz/inch (49 N/100 mm) 50 oz/inch (55 N/100 mm)

Tack	ASTM D 2979 Polyken™ Probe Tack 0.5 second dwell	37 oz (1150 g)
Tensile Strength and Elongation	ASTM D 1000 -Machine	45 lbs/inch (788 N/100 mm), 75%
Dielectric Strength	ASTM D 1000	7000 Volts

Performance properties tested on B-422 printed with the Brady Series R4900 and Brady Series R6000 Halogen Free ribbons. Printed samples of B-422 were laminated to aluminum and allowed to dwell 24 hours before exposure to the indicated environments. Unless noted, results are the same for both ribbons.

PERFORMANCE PROPERTIES	TEST METHOD	TYPICAL RESULTS
High Service Temperature	30 days at 212°F (100°C)	No visible effect
Low Service Temperature	30 days at -40°F (-40°C)	No visible effect
Humidity Resistance	30 days at 100°F (37°C) and 95% R.H.	No visible effect
UV Light Resistance	30 days in UV Sunlighter™ 100	No visible effect
Weatherability	ASTM G155, Cycle 1 30 days in Xenon Arc Weatherometer	No visible effect
Salt Fog Resistance	ASTM B 117 30 days in 5% salt fog solution chamber	No visible effect
Abrasion Resistance	Taber Abraser, CS-10 grinding wheels, 250 g/arm (Fed. STd. 191A, Method 5306)	R6000: Print legible after 100 cycles R6000 Halogen Free: Print legible after 100 cycles

PERFORMANCE PROPERTY	CHEMICAL RESISTANCE
----------------------	---------------------

Samples printed with the Brady Series R4900 and Brady Series R6000 Halogen Free ribbons. Samples laminated to aluminum panels and allowed to dwell 24 hours prior to testing. Test conducted at room temperature. Testing consisted of 5 cycles of 10 minute immersions in the specified test fluid followed by a 30 minute recovery period. After final immersion, samples rubbed 10 times with cotton swab saturated with test fluid.

CHEMICAL REAGENT	SUBJECTIVE OBSERVATION OF VISUAL CHANGE		
	EFFECT TO LABEL STOCK	R4900	R6000 Halogen Free
Methyl Ethyl Ketone	Slight adhesive ooze	No visible effect w/o rub, complete print removal after rub	No visible effect w/o rub, complete print removal after rub
1,1,1-Trichloroethane	Slight adhesive ooze	No visible effect w/o rub, complete print removal after rub	Obsolete
Toluene	Slight adhesive ooze	No visible effect w/o rub, complete print removal after rub	No visible effect w/o rub, severe print removal after rub
Freon® TMS	No visible effect	No visible effect w/o rub, slight print removal after rub	Obsolete
Isopropyl Alcohol	No visible effect	No visible effect	No visible effect
Mineral Spirits	No visible effect	No visible effect	No visible effect
JP-8 Jet Fuel	Slight adhesive ooze	No visible effect	No visible effect
ASTM #3 Oil	No visible effect	No visible effect	No visible effect
Mil 5606 Oil	No visible effect	No visible effect	No visible effect
Gasoline	Slight adhesive ooze	No visible effect w/o rub, slight print removal after rub	No visible effect
Skydrol® 500B-4	Slight adhesive ooze	No visible effect w/o rub, complete print removal after rub	No visible effect w/o rub, severe print removal after rub
Super Agitene®	No visible effect	No visible effect	No visible effect
BIOACT® EC-7R™	Slight adhesive ooze	No visible effect	Not tested
Deionized Water	No visible effect	No visible effect	No visible effect
3% Alconox® Detergent	No visible effect	No visible effect	No visible effect
10% Sodium Hydroxide Solution	No visible effect	No visible effect	No visible effect
10% Sulfuric Acid Solution	No visible effect	No visible effect	No visible effect

Shelf life is two years from the date of receipt for this product as long as this product is stored in its original packaging in an environment below 80° F (27° C) and 60% RH. It remains the responsibility of the user to assess the risk of using this product. We encourage customers to develop testing protocols that will qualify a product's fitness for use in their actual application.

Trademarks:

Alconox® is a registered trademark of Alconox Co.

BIOACT® is a registered trademark of Petroferm, Inc.

EC-7R™ is a trademark of Petroferm Inc.

Freon® is a registered trademark of Du Pont de Nemours, E.I. and Company

Polyken™ is a trademark of Testing Machines Inc.

Skydrol® is a registered trademark of the Monsanto Company

Sunlighter™ is a trademark of the Test Lab Apparatus Company

Super Agitene® is a registered trademark of Graymills Corporation

ASTM: American Society for Testing and Materials (U.S.A.)

CSA: Canadian Standards Association

UL: Underwriters Laboratories Inc. (U.S.A.)

All S.I. Units (metric) are mathematically derived from the U.S. Conventional Units

Note: All values shown are averages and should not be used for specification purposes.

Test data and test results contained in this document are for general information only and shall not be relied upon by Brady customers for designs and specifications, or be relied on as meeting specified performance criteria. Customers desiring to develop specifications or performance criteria for specific product applications should contact Brady for further information.

Product compliance information is based upon information provided by suppliers of the raw materials used by Brady to manufacture this product or based on results of testing using recognized analytical methods performed by a third party, independent laboratory. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

WARRANTY

Brady products are sold with the understanding that the buyers will test them in actual use and determine for themselves their adaptability to their intended uses. Brady warrants to the buyers that its products are free from defects in material and workmanship, but limits its obligation under this warranty to replacement of the product shown to Brady's satisfaction to have been defective at the time Brady sold it. This warranty does not extend to any persons obtaining the product from the buyers. This warranty is in lieu of any other warranty, express or implied, including, but not limited to, any implied warranty of merchantability or fitness for a particular purpose, and of any other obligations or liability on Brady's part. Under no circumstances will Brady be liable for any loss, damage, expense, or consequential damages of any kind arising in connection with the use, or inability to use, Brady's products.

Copyright 2019 Brady Worldwide, Inc. | All Rights Reserved
Material may not be reproduced or distributed in any form without written permission.

Brady North America | 6555 W. Good Hope Rd | Milwaukee, WI 53223 | USA | Tel: 414-358-6600 | Fax: 800-292-2289