

Specifications

Eaton CMS1-1-R

Eaton CMS1 inductor, 5.5 uH, 7 A, 4 PADS, SMT



Photo is representative



General specifications

| | |
|-----------------------------|--------------------|
| PRODUCT NAME | Eaton CMS inductor |
| CATALOG NUMBER | CMS1-1-R |
| UPC | 051712822428 |
| EAN | 5027590166737 |
| PRODUCT LENGTH/DEPTH | 9.4 mm |
| PRODUCT HEIGHT | 2.6 mm |
| PRODUCT WIDTH | 7.2 mm |
| PRODUCT WEIGHT | 0.24 g |
| COMPLIANCES | RoHS Compliant |
| GLOBAL CATALOG | CMS1-1-R |



Powering Business Worldwide

Product specifications

| | |
|------------------------------|---------------|
| TYPE | Inductor |
| MOUNTING | SMT |
| IRMS | 7 A |
| PACKAGE QUANTITY | 2000 |
| MATERIAL | Ferrite |
| FREQUENCY RATING | Up to 100 MHz |
| CONTACT CONFIGURATION | Four-pin |
| TEMPERATURE RATING | -40 to 160 °C |
| RESISTANCE | 0.0027 Ω |
| SIZE | Size 1 |
| TERMINALS | Four |
| SERIES | Common mode |

Resources

| | |
|--------------------------------------|--|
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - CMS1-1-R |
| | Eaton CMS common mode inductors surface mount data sheet |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

