



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Single Row Terminal Block

CB20220607EB

UPC:051712338318

### Dimensions:

- **Height:** .001 IN
- **Length:** 1.56 IN
- **Width:** .7 IN

**Weight:** .16 LB

### Warranties:

- Not Applicable

### Specifications:

- **Application:** industrial
- **Mounting:** Barrier end
- **Special Features:** Break down voltage 4100V
- **Type:** Closed back
- **Voltage Rating:** 300V
- **Number Of Poles:** Six-pole
- **Operating Temperature:** -40° to 105°C
- **Options:** Exit back terminals
- **Wire Size:** #22-12 AWG Cu
- **Torque Rating:** 9 lb-in
- **Center Spacing:** 0.375 in
- **Screw Options:** Stainless steel screw
- **Material:** Molded thermoplastic, nickel plated brass SEMS screw
- **Color:** Black
- **Connection:** #6-32 TPI screw
- **Terminal Material:** Printed circuit

### Supporting documents:

- [Product Catalog](#)

**Certifications:** No Data

### Product compliance:

- CE Marked
- RoHS Compliant



