


PXF6050BAA Datasheet

Product Name // 05 M, OM1 Multi Mode, Cabled, Flex fiber connector

 [View Product Page](#)



// **Product Description:**

- Flex Fiber Connector to LC type connector
 - Sealed to IP66, IP68, IP69K when mated with compatible connector
 - no cable options, or pre-terminated from 5M - 450M available
 - Duplex LC type fiber connector
- Choices of OS1, OM1 and OM3 cables for single or multimode
 - PXP6083 Sealing Cap available separately to maintain IP rating of unmated connectors
 - Mate with Inline fiber connector or panel mount connectors PXF6051, PXF6052

// **General Information:**

Product Display Title:	Flex Fiber Connector to LC type Connector
Product Family:	Circular Fiber Connectors
Product Series:	6000 Series - Duplex LC Fiber Buccaneer
Body Material:	Polyamide (PA)
Contact Type:	LC Fiber
Coupling Type:	30 Degree coupling
Diameter Over Coupling Ring Mm:	32mm
Fibre Mode:	OM1
Flamability Rating:	UL94V-0
Function:	Flex to Double LC Connector Double Ended Fiber Cable
Ip Rating:	IP66, IP68, IP69K
Max Operating Temperature:	+70°C
Min Operating Temperature:	-25°C

// **Product PDF Links**

 [6000 Series Fiber connectors...](#)

// **Product 3D CAD Model Links**

 [PXF6050BAA3D CAD Model](#)