


PXPTPU78FIM05ACL010PUR Datasheet

bulgin
an INFINITI® brand

Product Name // 5 Contacts 7/8" Inline Body Male 1m Cable

 View Product Page



// Product Description:

- 3 Contacts 7-8" Inline Body Male 1m Cable
 - IP67 rated when mated
 - Mechanical Cycles >100
- Operating Temperature -25°C to +85°C
 - Rated Voltage 300 V
 - ROHS compliance

// General Information:

Product Display Title:	7/8" Inline Body Male 1m Cable
Product Family:	Circular Automation Connectors
Product Series:	7/8" Series
Cable Length:	1m
Connection Method:	Solder
Contact Type:	Plug Contact
Current Max:	9A
Durability:	>100 Cycles
Function:	Inline Body Male Connector Single Ended Cable
Insulation Resistance:	>100MOhm
Ip Rating:	IP67
Max Cable Entry Size:	8.5mm
Max Operating Temperature:	+80°C
Min Operating Temperature:	-25°C
Number Of Contacts:	5 Contacts
Pin Layout Code:	A Code
Rohs Compliant:	Yes
Thread Size:	7/8-16UN
Voltage Max:	300V

// Product PDF Links

 78 Series Circular connectors...

// Product 3D CAD Model Links

 PXPTPU78FIM05ACL010PUR3D CAD Mode



Have a question or project enquiry
you'd like to talk to us about?



Click Here To Contact Us