


[Home](#) > [Search Tools](#) > [Part Number](#)

## Part Number Search

 You Searched For:  

**Note:** Data provided here are offered in good faith and are as reliable and accurate as possible. However, they do not form part of any contract of supply or purchase unless specifically confirmed in writing by an authorized representative of ITT. All information and images shown are the property of ITT ICS and are not to be reproduced in any form without direct authorization from ITT ICS.  
 ITT ICS strongly recommends that you contact your local ITT Sales Office for confirmation of all the details you obtain through these Web pages. Please be aware that data may change at any time and without notice. For a listing of Sales Offices, local sales support, and authorized distributors please use the "Global Sales Locator" located either to the right of this data or at the top of every page.

- [Sales Support](#)
- [Product Overview](#)
- [Stock Check](#)

Our Descriptive Part Number: DC51214


Our Global Manufacturing Part Number: 051214-0000

<input type="checkbox"/>	<b>CONSULT FACTORY</b>	RoHS compliant =	material restrictions of lead, cadmium, hexavalent chromium, mercury, poly bromated biphenyl ether (PBB) and poly bromide diphenyl ether (PBDE) according to directive 2002/95/EC
<input type="checkbox"/>	<b>CONSULT FACTORY</b>	RoHS compatible =	Compatible with lead free soldering process

### Export Compliance

<input type="checkbox"/>	Country of Compliance	United States
<input type="checkbox"/>	Export Compliance Notes	Commercial Shipments "C" Controlled by the US Department of Commerce.

### Product Datasheet

Thumbnail Image	
Product Group	D Subminiature Accessories
Where Sold	Asia Pacific, Americas, Europe
D Sub Accessory type	Plastic Endbell
Application Type	Commercial
Shell Size	DC
Cable Exit	Straight Cable Exit
Endbell Material	Thermoplastic, UL 94V-2 Rated. Color: Black.
Hardware Material	Steel
Hardware Finish	Yellow chromate over cadmium or zinc
Cable Entry	Ø17,63 (.694)
Dimension A	69,44 (2.734) ±0,38 (.015)
Dimension B	38,10 (1.500) ±0,38 (.015)
Dimension C	63,50 (2.500) ±0,13 (.005)
Dimension D	12,70 (.500) ±0,38 (.015)
Dimension F	17,63 (.694) ±0,25 (.010)
Dimension G	9,15 (.360) ±0,25 (.010)
Note 1	Kit consists of 1 shell, 1 cable clamp, 2 screws.
Note 2	Mounting hardware included, 2 screws #4-24 x 5/16 long self-tapping.
Note 3	Accommodates spring latches.
Footnote	Dimension are shown in mm (inch). Dimensions subject to change.
For more information	Please Contact Cannon Sales Department.