

Datasheet for part number MDVB1-37PH003K

| |
|--|
| Our Catalog Part Number: MDVB1-37PH003K |
| Our Global Manufacturing Part Number: 097342-0069 |
| Brand: Cannon Product Category: Micro Product Line: Micros Series: MICRO |

| Product Datasheet | |
|---------------------------------|---|
| Series | Micro D Plastic Shell - 0.050 inch spacing |
| Arrangement | 37 Contact |
| Gender | Pin |
| Contact Material | gold plated copper alloy |
| Contact Typ | crimp |
| Contact Resistance | 8 milliohms max. |
| Termination Type | 18" Min, M16874/4 #26AWG, Colored Code |
| Shell Material | Thermoplastic |
| Insulator Material | Polyester with mounting holes |
| Hardware | Jackscrew (standard) |
| Coupling | Jackscrew Coupling |
| Current Rating | 3 A max. |
| Dielectric Withstanding Voltage | 600 VAC at sea level 150 VAC at 70,00' altitude |
| Insulator Resistance | 5000 megohms min. |
| Thermal Shock | -55°/+125° |
| Physical Shock | 50 G's, 3 axes, 6 millisecond duration sawtooth pulse |
| Vibration | 20G's, 10-2000 Hz. 12 hours |
| Durability | 500 cycles of mating and unmating, 500 CPH max. |
| Moisture Resistance | Insulator resistance > 100 megohms |
| SaltSpray | 48 hours |