


P2 CONN TYPE	FIG NO	P1 CONN TYPE																																			
		PL20					UPL20					PL40					UPL40					PL123					UPL123										
		SCHEMATICS																																			
		E1	E2	E3	E4	E5	E1	E2	E3	E4	E5	E1	E2	E3	E4	E5	E1	E2	E3	E4	E5	E1	E2	E3	E4	E5	E1	E2	E3	E4	E5						
DASH NUMBERS																																					
BJ74	1A	-1	-2	-3	-4	-193	-5	-6	-7	-8	-194	-9	-10	-11	-12	-195	-13	-14	-15	-16	-196	-17	-18	-19	-20	-197	-21	-22	-23	-24	-198						
BJ74TL	1B	-25	-26	-27	-28	-199	-29	-30	-31	-32	-200	-33	-34	-35	-36	-201	-37	-38	-39	-40	-202	-41	-42	-43	-44	-203	-45	-46	-47	-48	-204						
BJ74FL	2A	-49	-50	-51	-52	-205	-53	-54	-55	-56	-206	-57	-58	-59	-60	-207	-61	-62	-63	-64	-208	-65	-66	-67	-68	-209	-69	-70	-71	-72	-210						
BJ374	2B	-73	-74	-75	-76	-211	-77	-78	-79	-80	-212	-81	-82	-83	-84	-213	-85	-86	-87	-88	-214	-89	-90	-91	-92	-215	-93	-94	-95	-96	-216						
BJ79	3A	-97	-98	-99	-100	-217	-101	-102	-103	-104	-218	-105	-106	-107	-108	-219	-109	-110	-111	-112	-220	-113	-114	-115	-116	-221	-117	-118	-119	-120	-222						
BJ79TL	3B	-121	-122	-123	-124	-223	-125	-126	-127	-128	-224	-129	-130	-131	-132	-225	-133	-134	-135	-136	-226	-137	-138	-139	-140	-227	-141	-142	-143	-144	-228						
BJ79FL	4A	-145	-146	-147	-148	-229	-149	-150	-151	-152	-230	-153	-154	-155	-156	-231	-157	-158	-159	-160	-232	-161	-162	-163	-164	-233	-165	-166	-167	-168	-234						
BJ379	4B	-169	-170	-171	-172	-235	-173	-174	-175	-176	-236	-177	-178	-179	-180	-237	-181	-182	-183	-184	-238	-185	-186	-187	-188	-239	-189	-190	-191	-192	-240						
BJ79TLRG	4A			-241						242						-243					-244																



DATA CONTAINED IN THIS DOCUMENT IS
PROPRIETARY TO TROMPETER ELECTRONICS, INC.
AND SHALL NOT BE DISCLOSED, COPIED OR USED
FOR PROCUREMENT OR MANUFACTURE WITHOUT
EXPRESS WRITTEN PERMISSION OF TROMPETER
ELECTRONICS, INC.

REVISIONS		12-09	SH 1
REV	DESCRIPTION	DATE	APPROVED
H	REVISED PER ECD 15720	11-23-04	WJ





RED INDICATES ORIGINAL

FIG 1A (P1)
-1 SHOWN
FIG 1B (P1)
-34 SHOWN





RECOMMENDED
PANEL CUTOUT
MAX PNL THK .140

FIG 2A (P1)
-67 SHOWN
FIG 2B (P1)
-81 SHOWN





RECOMMENDED
PANEL CUTOUT
MAX PNL THK .140

FIG 3A (P1)
-97 SHOWN
FIG 3B (P1)
-140 SHOWN



RECOMMENDED
PANEL CUTOUT
MAX PNL THK .109

FIG 4A (P1)
-149 SHOWN
FIG 4B (P1)
-177 SHOWN



RECOMMENDED
PANEL CUTOUT
MAX PNL THK .109

5. EXAMPLE OF COMPLETE MODEL NO:
AD - PL20 - E1 - BJ74
ADAPTER CONN P1 CONN P2 SCHEMATIC

4. EXAMPLE OF COMPLETE PART NO:
12-09 - 1
BASIC PART NO DASH NO

3. 50 & 75 OHM COAXIAL BNC/TNC/PUSH-ON PLUG
TO 2-LUG, 3-LUG, 4-LUG & THREADED CONCENTRIC TWINAXIAL/
TRIAxIAL INSULATED & NON-INSULATED BULKHEAD MOUNT JACKS

2. FINISH: TFS-1A (NICKEL)

1. ALL DIM ARE IN INCHES

INTERPRET DRAWING PER MIL-STD-100 DIMENSIONS ARE IN INCHES AND INCLUDE FINISH THICKNESS UNLESS OTHERWISE SPECIFIED		TOL: UNLESS SPECIFIED .XX .XXX .XXXX ANGLES		DRAWN AAH 11-22-04		DATE 11-22-04		MATERIAL:		FINISH:		TITLE: ADAPTERS: BNC/TNC PLUG SERIES TO CONCENTRIC TWINAX/TRIAx BULKHEAD MOUNT SERIES	
CHECKED 22D 11/23/04		QUALITY MS 11/23/04		MANU BP 11/23/04		APPROVED WJ 11/23/04		DO NOT SCALE DWG		SCALE 4/1		DATE 3-4-86	
NEXT ASSY		CAGE CODE 12-09H		SIZE B		CAGE CODE 14949		DRAWING NO. 12-09		REV. H		SHEET 1C	