

Datasheet for part number MKJCL1C11Z7-10DA

Our Catalog Part Number: MKJCL1C11Z7-10DA
Our Global Manufacturing Part Number: 155850-2780
Brand: Cannon Product Category: Circular Product Line: Trinity MKJ Series: MKJCL1

Product Datasheet	
Series	MKJ Clip Lock Miniature Circular Connector
Class	Potted Plug
Shell Style	Plug Flange Mount, Rotated 30 Degrees
Plating	Aluminum/Zinc Nickel, Black
Contact Arrangement	10 Contacts Size 23
Gender	Socket, PC Tail
Polarization	Normal (K1= 150° K2=210°)
Contact Size	#23
Wire Acomodiation	#22 - #28 AWG
Current Rating	5 Amps Maximum
Voltage Rating	500 VAC RMS Sea Level
Insulator Resitance	5000 Megaohms Minimum
Operating Temperature	-55°/+150°
Contact Resistance	8 Milliohms Maximum
Vibration	37 g per EIA-364-28, Cond. V; 30 g per MIL-STD-202, Method 204, Cond. G
Shock	300 g per EIA-364-27 Cond. D
Water Immersion	1 Meter for 1 hour
Mating Cylces	500