



Datasheet for part number DENGL-9S-P1

Our Catalog Part Number: DENGL-9S-P1
Our Global Manufacturing Part Number: 121584-0051
Brand: Cannon Product Category: D Sub Product Line: D Sub Series: D*NG

Product Datasheet	
General	Straight Pressfit Connector
Mating Cycles	50
Dielectric Withstanding Voltage	1200 VAC at sea level
Current Rating	5 A at 25°C 3.5 A at 70°C
Contact Resistance	10 milli Ohm max
Operating Temperature	-55°/+125°
Salt Spray Test	20 hours
Shell Material	steel
Shell Finish	tin
Insulator Material	Thermoplastic, type PCT UL 94V-0
Insulator Color	black
Contact Arrangement	9 contacts size 20
Gender	Socket
Contact Type	stamped
Contact Material	copper alloy
Contact Finish	gold flash (Performance Class 3)
Contact Termination	Right angled solder
Mounting Methode	90° Metal Bracket, M-3 Fastener, Boardlock