



Datasheet for part number ECCE3221-050S1A-ECCV0A

Our Catalog Part Number: ECCE3221-050S1A-ECCV0A			
Brand: Cannon	Product Category: EV	Product Line: EV	Series: ECCE JUMPER CABLE

Product Datasheet	
Series	EVC IEC 62196 Type 2 mode 3 connection cable
Product Image	
Current Rating	32A
Cable Rating	Level 2
Powering System	Single phase (250VAC)
Cable Length	5 m
Direction of Cable Strain Relief	Angled cable strain relief (90° Downwards)
Dust Cap	No dust cap
Modification Code 2nd Connector	Connection cable IEC Type 2 connector on 2-end
Direction of Cable Outlet	Straight cable strain relief
Temperature Range	-30°C to +50°C
Durability	10,000 mating cycles min
Sealing Requirements	IP 44 min per IEC 61851-1 and tested in accordance with IEC 60525
Certifications Connector	CE, ETL, IEC 62196-1 and IEC 62196-2
Certifications Cable	DIN EN 50620
Product Drawing	