



Datasheet for part number TFR12RA10

|   |
|---|
| Our Catalog Part Number: TFR12RA10  |
| Our Global Manufacturing Part Number: 121587-0034                             |
| Brand: Cannon Product Category: Trident Product Line: Trident Series: TSTRECT |

|                        |   |
|------------------------|---|
| Product Datasheet      |   |
| Series                 | Trident Flame Retardant Rectangular               |
| Operating Voltage      | Up to 250 V ac rms                                |
| Contact Current Rating | Up to 13 A  |
| Operating Temperature  | -55°C to +105°C                                   |
| Insulation Resistance  | 5000 Megaohms at 500 V dc                         |
| Durability             | Up to 500 Mating Cycles                           |
| Flammability Rating    | UL94-V0   |
| Number of Contacts     | 12  |
| Type                   | Panel Mounted Receptacle (without Contacts)       |
| Contact Type           | No Contacts delivered, please order separately.   |
| Colour                 | Insulator: Grey Polyamid for Railway Applications |