



Datasheet for part number DBMA-25P

|  |
|--|
| Our Catalog Part Number: DBMA-25P                                      |
| Our Global Manufacturing Part Number: 050911-0001                      |
| Brand: Cannon Product Category: D Sub Product Line: D Sub Series: D*MA |

| Product Datasheet               |  |
|---------------------------------|--|
| General                         | D*M High reliable D-Sub Connectors with crimp termination  |
| Wire Gauge Range AWG            | Standard: AWG 20-28. High Density: AWG 22-28   |
| Mating Cycles                   | 200  |
| Contact Arrangement             | 25 contacts size 20  |
| Dielectric Withstanding Voltage | 1000 VAC at sea level  |
| Current Rating                  | 7.5 A max  |
| Contact Resistance              | 10 milli Ohm max   |
| Operating Temperature           | -55°/+125°   |
| Salt Spray Test                 | 24 hours   |
| Shell Material                  | steel  |
| Shell Finish                    | Yellow chromate over zinc  |
| Insulator Material              | Thermoplastic, type PCT UL 94V-0   |
| Insulator Color                 | black  |
| Gender                          | Pin  |
| Contact Type                    | Crimp  |
| Contact Material                | copper alloy   |
| Contact Finish                  | gold over nickel   |
| Hardware                        | .120" (3,05mm) Through Hole  |
| Disclaimer                      | Our facility is not currently certified by the DLA and this product is not covered by the QPL/QML. |