



155334-0000

Part Number Details

Global Mfg Part No.	155334-0000
series	MKJ3
category	Circular
line	Trinity MKJ
brand	Cannon
ittPartNo	MKJ3B6F12-37SN

Series	Bayonet Coupling
Class	Environmental Plug and Receptacle Threaded Accessory Attachment
Shell Style	Straight Plug
Shell Size	6
Plating	Aluminum/Electroless Nickel
Contact Arrangement	23 Contacts Size 37
Gender	Socket, Crimp, Removable
Polarization	Normal (150° 210°)
Contact Size / Spacing	#23 / 0.076 inches (1.9 mm)
Wire Acomodiation	#22 - #28 AWG
Current Rating	5 Amps Maximum
Voltage Rating	500 VAC RMS Sea Level
Insulator Resitance	5000 Megaohms Minimum
Operating Temperature	-55°/+150°
Contact Resistance	8 Milliohms Maximum
Vibration	20 g' in Accordance with MIL-STD-1344 Method 2005, Condition IV
Shock	300 g' (MKJ1) 50 g' (MKJ0 and MKJ4) in Accordance with MIL-STD-1344 Method 2004, Condition E
EMI Shielding Effectiveness	40dB Attenuation, 100 MHz to 1000 MHz
rohsCompliantString	material restrictions of lead, cadmium, hexavalent chromium, mercury, poly bromated biphenyl ether (PBB) and poly bromide diphenyl ether (PBDE) according to directive 2011/65/EU
rohsCompliantFlag	YES

A datasheet is available for download.

[Download Datasheet PDF](#)

Check the stock availability of this product at our distributors.

Check Stock Now

Part Number	Distributor	Qty	Location
-------------	-------------	-----	----------

Note: Data provided here are offered in good faith and are as reliable and accurate as possible. However, they do not form part of any contract of supply or purchase unless specifically confirmed in writing by an authorized representative of ITT. All information and images shown are the property of ITT ICS and are not to be reproduced in any form without direct authorization from ITT ICS. ITT ICS strongly recommends that you contact your local ITT Sales Office for confirmation of all the details you obtain through these Web pages. Please be aware that data may change at any time and without notice. For a listing of Sales Offices, local sales support, and authorized distributors please use the "Contact Us" at the top of every page.

globalManufPartNo: 155334-0000; line: Trinity MKJ; ittPartNo: MKJ3B6F12-37SN

[Request a Quote](#)