

Eaton BAB thermal magnetic circuit breaker

BAB3100H

UPC:786679304006

Dimensions:

- **Height:** 2.9 IN
- **Length:** 2.9 IN
- **Width:** 3 IN

Weight:1 LB

Notes:HACR rated

Warranties:

- 1 year

Specifications:

- **Type:** Quicklag industrial thermal-magnetic circuit breaker
- **Special Features:** Bolt-on mounting
- **Amperage Rating:** 100A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 240V
- **Trip Type:** Non-Interchangeable
- **Quantity:** Q32
- **Circuit Breaker Type:** BAB

Supporting documents:

- [Loadcenters and Circuit Breakers](#)
- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - BAB3100H](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance: No Data



