

## NGR Rocker Switch Base

**NGR10041BG00N**

**UPC:**786685608174

**Dimensions:**

- **Height:** 5 IN
- **Length:** 13 IN
- **Width:** 12 IN

**Weight:**8 LB

**Warranties:**

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warranted for one (1) year from the date of shipment.

**Specifications:**

- **Type:** No rocker assembled
- **Amperage Rating:** 15A at 125 Vac, 10A at 250 Vac, 15A at 28 Vdc
- **Circuit Number:** 1004
- **Circuit Position Center:** OFF
- **Circuit Position Down:** ON
- **Contact Material:** Gold plated
- **Frame Color:** Black
- **Mounting:** Snap-in
- **Number Of Poles:** Single-pole
- **Style:** Rocker and paddle frame
- **Terminals:** 0.250 in spade terminal
- **Texture:** Matte
- **Throw Type:** Double-throw

**Supporting documents:**

- [Eatons Volume 11-Vehicle and Commercial Controls](#)
- [Eaton Specification Sheet - NGR10041BG00N](#)

**Certifications:**

- UL Listed
- CSA Certified

**Product compliance:**

- RoHS Compliant

---

© 2016 Eaton. All rights reserved.