

Specifications



Photo is representative

Eaton SL7-FL24-A

Eaton Light Module, SL7, 70 mm, Strobe LED, 24 Vac/Vdc, Amber, 1.4 Hz, (1), UL type 4, 4X, 13 , IP66

General specifications

PRODUCT NAME	Eaton SL7 stacklight module
CATALOG NUMBER	SL7-FL24-A
EAN	4015081679393
PRODUCT LENGTH/DEPTH	3.25 in
PRODUCT HEIGHT	3 in
PRODUCT WIDTH	3 in
PRODUCT WEIGHT	0.25 lb
COMPLIANCES	CE Marked
CERTIFICATIONS	cULus Listed CSA Certified UL Listed UL 508 UL Listed file E29184 CSA Std. C22.2 No. 94-91 CSA Std. C22.2 No. 14-10 CSA Class No. NKCR7 IEC Rated
CATALOG NOTES	0



Powering Business Worldwide

Product specifications

TYPE	70 mm
ENVIRONMENTAL RATING	IP66
VOLTAGE RATING	24 Vac/Vdc
FREQUENCY RATING	1.4 Hz
ILLUMINATION	Strobe LED
COLOR	Amber
QUANTITY	1
ENCLOSURE	UL type 4, 4X, 13
SERIES	SL7

Resources

SPECIFICATIONS AND
DATASHEETS

[Eaton Specification Sheet -
SL7-FL24-A](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

