

Specifications



Photo is representative

Eaton 2584A-125-C1

Eaton Crouse-Hinds series Pauluhn 25B receptacle, 15A/20A, Copper-free aluminum, Surface, 5-15/20R, Through feed, 1/2", Two receptacles, 125 Vac

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Pauluhn 25B receptacle
CATALOG NUMBER	2584A-125-C1
UPC	662276378933
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	5.5 in
PRODUCT WIDTH	2.88 in
PRODUCT WEIGHT	1.7 lb

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
----------------------------	----------------------------------

INGRESS PROTECTION (IP) RATINGS	IP66
--	------

Product specifications

MATERIAL	Copper-free aluminum
-----------------	----------------------

MOUNTING METHOD	Surface
------------------------	---------

TYPE	Two receptacles
-------------	-----------------

AMPERAGE RATING	15A/20A
------------------------	---------

STYLE	Through feed
--------------	--------------

TRADE SIZE	1/2"
-------------------	------

NEMA CONFIGURATION	5-15/20R
---------------------------	----------

VOLTAGE RATING	125 Vac
-----------------------	---------

Resources

CATALOGS	Pauluhn Marine Watertight ANSI NEMA Receptacles and Plugs catalog page
-----------------	--

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - 2584A-125-C1
--------------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.