

Specifications



Photo is representative

Eaton

ADE1CN0752NPSCN

Eaton Crouse-Hinds series Capri ADE-1FC cable gland, TSC Compound, 2 (M), Straight, Gland size 6, Non-armoured Barrier, Nickel plated brass, 8.5-16 outer sheath, Flameproof and increased safety, Silicone seal, 3/4" NPT

General specifications

PRODUCT NAME	Eaton's Crouse-Hinds series Capri ADE-1FC cable gland
CATALOG NUMBER	ADE1CN0752NPSCN
EAN	3589350031423
PRODUCT LENGTH/DEPTH	70.5 mm
PRODUCT HEIGHT	33 mm
PRODUCT WIDTH	30 mm
PRODUCT WEIGHT	200.151 g



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	IECEX/ATEX NEC/CEC IEC
NEC HAZARDOUS RATING	Class I, Division 2 Class I, Division 1 Class I, Zone 2
IECEX/ATEX HAZARDOUS RATING	Zone 2 Zone 21 Zone 22 Zone 1
INGRESS PROTECTION (IP) RATINGS	IP68 IP66

Product specifications

PROTECTION TYPE	Flameproof and increased safety
GLAND TYPE	Non-armoured Barrier
THREAD SIZE	3/4"
THREAD TYPE	NPT
CABLE SEALING RANGE	2 (M)
OUTER SHEATH (MIN/MAX)	8.5-16
GLAND SIZE	6
SEALING TYPE	Silicone
MATERIAL	Nickel plated brass
BARRIER TYPE	TSC Compound
CONNECTOR TYPE	Straight

Resources

TECHNICAL DATA SHEETS [ADE-1FC Datasheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.