

Specifications

Photo is representative

Eaton ADE1M162NPNK1

Eaton Crouse-Hinds series Capri ADE-1F2 cable gland, 2 (M), Straight, Gland size 4, Non-armoured, Nickel plated brass, 4.5-8.5 outer sheath, Flameproof and increased safety, Silicone seal, Locknut, green composite washer, M16 Metric

General specifications

PRODUCT NAME	Eaton's Crouse-Hinds series Capri ADE-1F2 cable gland
CATALOG NUMBER	ADE1M162NPNK1
EAN	3589350050301
PRODUCT LENGTH/DEPTH	40 mm
PRODUCT HEIGHT	20.9 mm
PRODUCT WIDTH	19 mm
PRODUCT WEIGHT	41.017 g



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	IEC NEC/CEC IECEX/ATEX
NEC HAZARDOUS RATING	Class I, Zone 1 Class I, Zone 2
IECEX/ATEX HAZARDOUS RATING	Zone 2 Zone 21 Zone 1 Zone 22
INGRESS PROTECTION (IP) RATINGS	IP68 IP66

Product specifications

PROTECTION TYPE	Flameproof and increased safety
GLAND TYPE	Non-armoured
THREAD SIZE	M16
THREAD TYPE	Metric
CABLE SEALING RANGE	2 (M)
OUTER SHEATH (MIN/MAX)	4.5-8.5
GLAND SIZE	4
SEALING TYPE	Silicone
MATERIAL	Nickel plated brass
CONNECTOR TYPE	Straight
SPECIAL FEATURES	Locknut and green composite washer

Resources

TECHNICAL DATA SHEETS [ADE-1F2 Datasheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.