

Specifications

Photo is representative

Eaton E-Z1016-8818

Eaton Crouse-Hinds series Cam-Lok J Series E-Z1016 plug, Up to 190A continuous, #6-#2 AWG, Black, Double set screw, Brass contacts, Male, Thermoplastic elastomer (TPE), Non-vulcanized, 600 Vac/dc

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Cam-Lok J Series E-Z1016 plug
CATALOG NUMBER	E-Z1016-8818
UPC	662275338273
PRODUCT LENGTH/DEPTH	7.14 in
PRODUCT HEIGHT	1.49 in
PRODUCT WIDTH	1.49 in
PRODUCT WEIGHT	0.6 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	3R

Product specifications

CABLE SIZE	#6-#2 AWG
AMPERAGE RATING	Up to 190A Continuous
VOLTAGE RATING	600 Vac/dc
MATERIAL	Thermoplastic elastomer (TPE)
TYPE	Non-vulcanized
CONNECTION TYPE	Double set screw
GENDER	Male
COLOR	Black
CONTACT MATERIAL	Brass

Resources

BROCHURES	Cam-Lok Single Pole Plugs and Receptacles catalog
CATALOGS	Cam-Lok J Series Single Pole Plugs and Receptacles catalog page
INSTALLATION INSTRUCTIONS	IM 1012 - Cam-Lok E-Z1016 and E-Z1018 Connectors
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - E-Z1016-8818

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.