



Part #, Drawing, Series

MICRO D

[HOME](#) > [PRODUCTS](#) > [HIGH REL](#) > [MICROD](#) > [PRODUCT DETAILS](#)

C115366-9227C MDM JACKPOST SERIES MDM JACKPOST



FEATURES AND BENEFITS

- Female screw lock for MDM Connectors
- Flight and Engineering models available
- Standard panel, Savers and Feedthrough
- Non-outgassing
- Order 1 part-numbers per connector

TYPICAL APPLICATIONS

- Space equipments
- Satellites harnesses and payloads
- Launchers
- Engineering
- Military and Avionics

ASSOCIATED PRODUCTS

- [MDM Connector](#)
- [MDMA Connectors](#)

Image shown represents the product series and may not indicate the actual part number

TOOLBOX

- [Product Selection Guide](#)
- [Sales Locator](#)

DOWNLOADS

- [Datasheet](#)

CONTACT TECH SUPPORT

SEARCH DISTRIBUTOR STOCK

REQUEST SAMPLE

SPECIFICATIONS

Torque value - Standard - Male Side: 0.44 Nm min / 0.48 Nm max

Torque value - Standard - Female Side: 0.28 Nm min / 0.32 Nm max

Torque value - FR136/FR139 - Male Side: 0.44 Nm min / 0.48 Nm max

Torque value - FR136/FR139 - Female Side: 0.28 Nm min / 0.32 Nm max

Torque value - Savers - Male Side: 0.36 Nm min / 0.40 Nm max

Torque value - Savers - Female Side: 0.28 Nm min / 0.32 Nm max

Temperature range: -55°C to 125°C

C115366-9227C

Description: MDM-115366-9227C

Quality Level: According to ESCC Specification

Number of Contacts: Not Applicable

Contact Type: Not Applicable

Wire Size: Not Applicable

Fixing Option: Not Applicable

Termination Type:	Not Applicable
Wire Length:	Not Applicable
Cable Type:	Not Applicable
Outlet:	Not Applicable
Shell Finish:	Not Applicable
Application:	FR136/FR139 versions
Panel Mounting:	Rear Mounting
Panel Thickness:	1.6mm
Nut Type:	NA

We use cookies to provide our customers with an optimal site experience. View our [Privacy Policy](#) to learn more about how we use cookies and how to manage your settings. By proceeding on our website, you consent to the use of cookies. [Yes](#) [No](#)