



Part #, Drawing, Series

D-SUB

HOME > PRODUCTS > HIGH REL > D SUB > PRODUCT DETAILS

C115368-3214 D*MA CONNECTOR SERIES D-SUB CONNECTORS WITH REMOVABLE CRIMP CONTACTS



FEATURES AND BENEFITS

- removable crimp contacts technology
- Flight and Engineering models available
- 6 shell sizes: E, A, B, C, D and F
- Standard density: 9,15, 25, 37, 50 contacts
- High density: 15, 26, 44, 62, 78, 104 contacts
- Supplied with or without contacts
- Non-outgassing

TYPICAL APPLICATIONS

- Space equipments
- Satellites harnesses and payloads
- Launchers
- Engineering
- Military and Avionics

ASSOCIATED PRODUCTS

- [D*MA Crimp Contacts](#)
- [D*BMA Savers](#)
- [D*M Jackscrew](#)
- [D*M Backshell](#)
- [D*M Dust Cap](#)
- [D*M Connector](#)

Image shown represents the product series and may not indicate the actual part number

TOOLBOX

- [Product Selection Guide](#)
- [Sales Locator](#)

DOWNLOADS

- [Datasheet](#)

CONTACT TECH SUPPORT

SEARCH DISTRIBUTOR STOCK

REQUEST SAMPLE

SPECIFICATIONS

Working Voltage Standard Density:	300 Vrms at sea level - 250 Vrms at 33000m altitude
Working Voltage High Density:	250 Vrms at sea level - 200 Vrms at 33000m altitude
Rated current Contact Standard Density size 20/20:	7.5 A
Rated current Contact Standard Density size 20/18:	7.5 A
Rated current Contact Standard Density size 20/26:	3.0 A
Rated current Contact High Density size 22/22:	5.0 A
Contact resistance (rated current):	5.0 milliohms max
Insulation resistance (500 VDC):	5000 megohms min
Voltage proof Standard Density:	1250 Vrms / 2.0 mA leakage current

Voltage proof High Density:	1000 Vrms / 2.0 mA leakage current
temperature range:	-55°C to 125°C
residual magnetism level:	200 Gamma (NMB)

C115368-3214

Description:	DBMA44PNMB-FR022-FO
Quality Level:	Engineering Model
Variant:	High Density
Application:	Not Applicable
Head Type:	Not Applicable
Shell Size:	B
Number of Contacts:	44
Contacts Arrangement:	Not Applicable
Contact Type:	Pin (Male)
Contact Size:	Not Applicable
Wire Type or Size:	Not Applicable
Outlet:	Not Applicable
Weight Variant:	Not Applicable
Backshell and Haloring Variant:	Not Applicable
Fixing Option:	Through Hole (no hardware)
Bracket:	Not Applicable
Termination Type:	Not Applicable
Termination Diameter:	Not Applicable
Termination Distance Between Two Rows:	Not Applicable
Foot Print:	Not Applicable
Contact Delivered:	Without contact
Material:	Not Applicable
Shell Finish:	Gold
Finish:	Not Applicable



[Sitemap](#)
[Careers](#)

[Terms & Conditions](#)

[Legal](#)

[Privacy](#)

[Do Not Sell My Personal Information](#)



We use cookies to provide our customers with an optimal site experience. View our [privacy policy](#) to learn more about how we use cookies and how to manage your settings. By proceeding on our website, you consent to the use of cookies. [Yes](#) [No](#)