



Part #, Drawing, Series

NEW

D-SUB

[HOME](#) > [PRODUCTS](#) > [HIGH REL](#) > [DSUB](#) > [PRODUCT DETAILS](#)

C115440-0013A D*M COMBO CONTACTS SERIES D-SUB REMOVABLE CONTACTS FOR COMBO CONNECTORS



Image shown represents the product series and may not indicate the actual part number

FEATURES AND BENEFITS

- Power and Coax Contacts for Combo Connector
- Flight and Engineering models available
- Non-outgassing

TYPICAL APPLICATIONS

- Space equipments
- Test equipments
- Satellites harnesses and payloads
- Launchers
- Engineering
- Military and Avionics

ASSOCIATED PRODUCTS

- [D*M Combo Connector](#)

SPECIFICATIONS

Working Voltage Coax Contacts:	100 Vrms at sea level - 100 Vrms at 33000m altitude
Working Voltage Power Contacts:	250 Vrms at sea level - 250 Vrms at 33000m altitude
Rated current Coax Center Contact:	7.5 A
Rated current Power Contact:	40.0 A / Limitation by current carrying capability of cable
Contact resistance Coax Contacts (rated current):	7.0 milliohms max
Contact resistance Power Contacts (rated current):	2.0 milliohms max
Coax Contacts Frequency Range:	Up to 1 GHz
Coax Contacts VSWR (up to 1 GHz):	1.4
Coax Contacts RF Insertion Loss at 1 GHz:	0.2 dB
Voltage proof Coax Contacts (Straight termination):	1000 Vrms
Voltage proof Coax Contacts (90° termination):	800 Vrms
temperature range:	-55°C to 125°C

TOOLBOX

- [Product Selection Guide](#)
- [Sales Locator](#)

DOWNLOADS

- [Datasheet](#)

CONTACT TECH SUPPORT

SEARCH DISTRIBUTOR STOCK

REQUEST SAMPLE

C115440-0013A

Description:	DM115440-0013-FR022
Quality Level:	Engineering Model
Variant:	Power
Application:	Not Applicable
Head Type:	Not Applicable
Shell Size:	Not Applicable
Number of Contacts:	Not Applicable
Contacts Arrangement:	Not Applicable
Contact Type:	Socket (Female)
Contact Size:	Not Applicable
Wire Type or Size:	NA
Outlet:	Not Applicable
Weight Variant:	Not Applicable
Backshell and Haloring Variant:	Not Applicable
Fixing Option:	Not Applicable
Bracket:	Not Applicable
Termination Type:	90° PCB
Termination Diameter:	Not Applicable
Termination Distance Between Two Rows:	Not Applicable
Foot Print:	Not Applicable
Contact Delivered:	Not Applicable
Material:	Not Applicable
Shell Finish:	Not Applicable
Finish:	Not Applicable

