



PUSHBUTTON

HOME > PRODUCTS > SWITCHES > PUSHBUTTON > PRODUCT DETAILS

EP12SD1AVGE EP SERIES SEALED TINY PUSHBUTTON SWITCHES



The EP series of sealed tiny pushbutton switches from C&K are selected to power applications in the telecommunications and networking industry. The EP's snap-fitting actuator accepts standard caps, and is sealed to protect against solder and cleaning processes - helping ensure it can withstand any harsh environment. Available in thru-hole and surface mount models, C&K's EP switches are also RoHS compliant.

FEATURES AND BENEFITS

- Snap-fitting actuator accepts standard caps
- Sealed against solder & cleaning processes
- Thru-hole and surface mount models
- Telecommunications & networking equipment
- Instrumentation & controls
- Computers & peripherals

SPECIFICATIONS

Contact Rating:	Gold contact material: 0.4 VA max. @ 20 V AC or DC max. See datasheet for additional ratings
Contact Resistance:	Below 20 milliohms typ. initial @ 2-4 V DC, 100 mA, for both silver and gold plated contacts
Electrical Life:	EP11, EP21 models: 60,000 make-and-break cycles at full load. EP12 models: 30,000 cycles
Solderability:	Per MIL-STD-202F method 208D, or EIA RS-186E method 9 (1 hour steam aging)
Dielectric Strength:	1,000 Vrms min. @ sea level
Insulation Resistance:	10 ⁹ ohms min.
Operating Temperature:	-30°C to 85°C
Certifications:	models available

EP12SD1AVGE

Most Common:	No
Current Rating:	1A (AC/DC)
Circuit:	SPDT
Mounting Type:	Thru-hole, Right Angle, Vertical
Sealing:	Sealed - IP57
Illumination:	None
Switch Function:	On-Mom
Electrical Life Cycles:	30,000
Voltage Rating - AC:	120V
Voltage Rating - DC:	28V
Actuator Type:	Round, Plunger
Color - Actuator/Cap:	Black
Illumination Type, Color:	
Illumination Voltage (Nominal):	
Termination Style:	Thru-hole, Right Angle
Additional Features:	Epoxy Sealed Terminals
Panel Cutout Dimensions:	
Packaging:	Tray

Image shown represents the product series and may not indicate the actual part number

TOOLBOX Product Selection Guide Sales Locator	DOWNLOADS Datasheet Complete Product Line
--	--

[CONTACT TECH SUPPORT](#)

[SEARCH DISTRIBUTOR STOCK](#)

[REQUEST SAMPLE](#)

[3D MODEL](#)

