



Part No: 101B10029X

Product Description

- DIN 41617
- Male connector
- 21-pos.
- Solder pin
- 5,0 mm

[Inquiry](#)

General Data

Technical Data

Material Data

Downloads

min. working temperature	-55° C
max. working temperature	+125° C
Contact resistance standard	15 mOhm
Extraction force	33 N
Insertion force	33 N
Quality class	Quality class 2
Mating cycles	400
Insulation resistance	10 GOhm