

Image gallery

3D view



## Part No: 101B10079X

### Product Description

- DIN 41617
- Male connector
- 13-pos.
- Solder pin angled
- 2,5 mm

Inquiry

General Data

Technical Data

Material Data

Downloads

|                             |                 |
|-----------------------------|-----------------|
| min. working temperature    | -55° C          |
| max. working temperature    | +125° C         |
| Contact resistance standard | 15 mOhm         |
| Extraction force            | 32 N            |
| Insertion force             | 32 N            |
| Quality class               | Quality class 2 |
| Mating cycles               | 400             |
| Insulation resistance       | 10 GOhm         |