

Image gallery

3D view



Part No: 102A10059X

Product Description

- DIN 41617
- Female Connector
- 13-pos.
- Solder pin
- 5,0 mm

Inquiry

General Data

Technical Data

Material Data

Downloads

min. working temperature	-25° C
max. working temperature	+85° C
Contact resistance standard	15 mOhm
Extraction force	32 N
Insertion force	32 N
Quality class	Quality class 3
Mating cycles	50
Insulation resistance	10 GOhm