



Part No: 102E10059X

Product Description

- DIN 41617
- Female Connector
- 13-pos.
- Solder pin
- 5,0 mm

[Inquiry](#)

General Data

Technical Data

Material Data

Downloads

min. working temperature	-65° C
max. working temperature	+125° C
Contact resistance standard	15 mOhm
Extraction force	30 N
Insertion force	30 N
Mating cycles	500
Insulation resistance	10 GOhm