

Image gallery

3D view



Part No: 131A34019X

Product Description

- Combination D-SUB contacts
- Plug
- 75 Ohm
- Solder pin straight

[Inquiry](#)

General Data

Technical Data

Material Data

Standards

Downloads

Dielectric with standing voltage coaxial	750 V
min. working temperature	-55° C
Working voltage coaxial	250 V
Quality class	Quality class 3
Mating cycles	50
IP rating	IP 20
Impedance coax	75 Ohm
Frequency range	0- 2 Ghz
Insertion force	7 N
Extraction force	7 N
Coaxial resistance standard	2,7 mOhm