Image gallery | 3D view









Part No: 132C13060X

Product Description

- Combination D-SUB contacts
- Socket
- Solder pin angled

Inquiry

General Data | Technical Data | Material Data | Standards | Downloads

Dielectric with standing voltage power	1000 V
min. working temperature	-55° C
Working voltage power	250 V
Quality class	Quality class 1
Mating cycles	500
IP rating	IP 20
Current rating power	20 A
Insertion force	7 N
Extraction force	5 N
Power resistance standard	1 mOhm