Image gallery | 3D view









Part No: 15-000553

Product Description

- IP67 D-SUB High Density Solid Body
- 44-pos.
- Socket
- Solder pin straight

Inquiry

General Data | Technical Data | Material Data | Standards | Downloads

Dielectric with standing voltage signal	1000 V
Quality class	Quality class 3
Mating cycles	50
IP rating	IP67
Insertion force	120 N
Extraction force	120 N
Contact resistance standard	10 mOhm
min. working temperature	-40° C
max. working temperature	+105° C