

Image gallery

3D view



Part No: 15-000563

Product Description

- IP67 D-SUB High Density Solid Body
- 62-pos.
- Socket
- Solder pin straight

[Inquiry](#)

General Data

Technical Data

Material Data

Standards

Downloads

Dielectric with standing voltage signal	1000 V
Quality class	Quality class 3
Mating cycles	50
IP rating	IP67
Insertion force	170 N
Extraction force	170 N
Contact resistance standard	10 mOhm
min. working temperature	-40° C
max. working temperature	+105° C